
sIRoCube

The stationary modular NIR-Spectrometer for touchless measuring of plastics



Technology by **IoSys** – Europe's Leading Specialist for Plastic Detection



With the near infrared spectrometry (NIR) of the IoSys units it is possible to identify bigger plastic parts of the household-, engineering electronics fields. It allows direct analysis of non-dark-colored plastic parts and other materials like carpets and textiles.

The measuring principle is the diffuse near infrared reflection spectroscopy where the characteristic absorption patterns of different polymer types in a typical spectral region are used. The polymer sample is radiated with infrared light and the reflected light of the measuring place is analyzed by a near infrared detector array.

For plastic identification the samples are quickly passing by below the optical focus lens, for instance using a conveyor belt. The light focus (ca. 4 - 6 cm) of the movable NIR light source can be adjusted for distances from 30 up to 60 cm. By the integrated relay-inter-face board the identi-

fication result is also generated as output signal for sorting systems. Detected polymer types and the corresponding relay positions can be set individually. A 9-pole-SUB-D connector enables individual cable wiring. Additionally the online result can be shown on an external VGA screen.

The device includes the optical NIR-system and the computer, which controls and evaluates the identification process. Control and parameter settings like model selection can be set by the integrated LCD-touchscreen, by an external keyboard or by an external optional colour touch-screen. Additional connections like an USB-interface enables external data transfer. An LED array visualizing the identification result is available as an option as well as an external touchscreen.





The **sIRoCube** design enables to set up several units in parallel to measure the whole width of a conveyor belt.

The identification of different plastic types is the result of a trained pattern recognition with a specially developed neural network inside a database with several counterchecking. The result of the calculation is a list of the most probable polymer types identified within a probability between 0 and 100%. This comparison is necessary, since – contrary to metals – plastics have no norms and no standardizations!

Furthermore up to 7 pre-set polymer types can be programmed with corresponding external signal generation.

The software allows detailed spectra viewing, helps to develop own measuring applications

Technical Data:

- Dimensions: 270 x 270 x 100 mm

- Weight: ca. 2,7 kg

100 - 230 VAC, 50/60 Hz - Power Supply:

Optional Accessories:

- External VGA-Screen for the display of results
- External touchscreen for display and operation
- External printer for result documentation
- LED-Array for the visual indication of the measuring results

Specifics of the unit:

- Identification of plastics from household-, packaging and engineering/electronics waste
- Contactless and non-destroying measurements
- Measuring time within few milliseconds
- Sample distance up to 60 cm
- Online setup for conveyer belt application
- Detailed spectra overview for easy comparison
- 7 individually programmable outputs for signal generation

Following plastic types are in the standard database:

PA6/PA66	PS	PC+ABS	ABS+PVC	PLA
PA12 PE	PP0 SAN	PBT PET	PVC PE+PA	Cellulose
PP	PC+PET	PMMA	PE+PET	
ABS	PC	POM	PP+PET	

